WALL/KILN SPACING: 12" [30.5cm] SPACING BETWEEN SIDES OF KILN AND WALLS OR OTHER OBJECTS. 18" [45.7cm] IS RECOMMENDED. LEAVE AT LEAST 18" [45.7cm] BETWEEN TWO KILNS.

AMBIENT VENTILATION: SEE CHART BELOW FOR RATINGS. TO CALCULATE

REQUIREMENTS, SEE hotkilns.com/calculate-kiln-room-ventilation.

KILN VENTILATION: L&L VENT-SURE KILN VENT RECOMMENDED FOR SAFETY

AND LONGER ELEMENT LIFE. OPTIONAL CONTROL ALLOWS VENT TO BE TURNED ON AND OFF WITH CONTROL.

MADE FROM

NEW

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L&L KILN MFG INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF L&L KILN MFG INC. IS PROHIBITED.

DRAWN BY DATE

SCALE

5

DSL 05/01/20 1:18

OTHER INFO: REFER TO INSTALLATION INSTRUCTIONS AND CAUTIONS INSTRUCTIONS FOR OTHER REQUIREMENTS AND SAFETY INFORMATION. REFER TO WIRING DIAGRAM FOR ELECTRICAL HOOKUP INFORMATION.

MAX LOAD WEIGHT: SEE hotkilns.com/load-weight

T3436-BL (3" BRICK) DAVINCI BELL-LIFT GENERAL DIMENSIONS

WEIGHT OF KILN: 1905 LBS, 864 KG

CLEARANCES, LAYOUT & INSTALLATION

1/4 | 300-001-64







